
















	CONNECTION TYPE	ACTIVATION TYPE	ACTIVATION SURFACE	FEEDBACK	PLUG SIZE	MOUNTING
 Buddy Button AT16204	Wired; cord length 5 ft.	Pressure; 3.5 oz. activating force	2.5" padded bar	Auditory click, Tactile	1/8 in. / 3.5 mm mono	Universal Mounting Plate
 Big Red AT16207	Wired; cord length 6 ft.	Pressure; 5.5 oz. activating force	5" diameter	Auditory click, Visual, Tactile	1/8 in. / 3.5 mm mono	Quick Ready Mounting Plate
 Jelly Bean AT16228	Wired; cord length 6 ft.	Light pressure; 2.5 oz. activating force	2.5" diameter	Auditory click, Tactile	1/8 in. / 3.5 mm mono	Universal Mounting Plate
 Jelly Beamer Transmitter AT16263	Wireless	Light pressure; 2.5 oz. activating force	2.5" diameter	Auditory click, Tactile	n/a ; requires the Original Receiver	Universal Mounting Plate
 Big Beamer Transmitter AT16264	Wireless	Pressure; 5.5 oz. activating force	5" diameter	Auditory click, Visual, Tactile	n/a ; requires the Original Receiver	Universal Mounting Plate
 Textured Saucer Switches AT77710	Wired	Light touch; .88oz. activating force	7" diameter	Auditory click, Tactile	1/8 in. / 3.5 mm mono	Velcro

		CONNECTION TYPE	ACTIVATION TYPE	ACTIVATION SURFACE	FEEDBACK	PLUG SIZE	MOUNTING
	Gooshy Switch AT77715	Wired	Pressure; 3.17 oz. activating force	10" L x 4.5" W x 2" H	Auditory click, Tactile	1/8 in. / 3.5 mm mono	Velcro
	Wobble Switch AT83130	Wired; cord length 5.2 ft.	Pressure; 2.8 oz. activating force	4.3" padded bar	Auditory click, Tactile	1/8 in. / 3.5 mm mono	Attachment screw: 1/4 in., Whitworth thread
	Pillow Switch AT16241	Wired; cord length 5 ft.	Pressure; 6 oz. activating force	3.3" diameter	Auditory click, Tactile	1/8 in. / 3.5 mm mono	Included Velcro and Safety Pin
	Spec Switch AT16257	Wired; cord length 6 ft.	Light pressure; 3.5 oz. activating force	1.375" diameter	Auditory click, Tactile	1/8 in. / 3.5 mm mono	Universal Mounting Plate
	Micro Light Switch AT16206	Wired; cord length 5 ft.	Light pressure; 0.4 oz. activating force	1.7" x 0.5"	Auditory click, Tactile	1/8 in. / 3.5 mm mono right angle	Quick Ready Mounting Plate
	Honey Bee Proximity Switch AT83301	Wired; cord length 30 in.	Proximity Sensor with adjustable sensing range	3" x 1.5" x 0.5"	Auditory	1/8 in. / 3.5 mm mono	n/a
	Little Candy Corn 2 AT16266	Wired; cord length 6 ft.	Proximity Sensor	2" L x 2" W x 0.625" H	Auditory and visual (can be turned off)	1/8 in. / 3.5 mm mono (TS) plug	Quick Ready Mounting Plate or integrated threaded inserts